

Specification Sheet

Part Number: RT150LEP0X2



Releasable Cable Tie, Release Tab, 32.3" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number	115-00038
Type	RT150LEP
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special design with extended pawl offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.
Quantity Per	bag

Product Description

HellermannTyton Releasable Cable Ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Releasable Cable Tie, Release Tab, 32.3" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name

RT150LEP-PA66-BK

Minimum Tensile Strength (Imperial)

175.0

Minimum Tensile Strength (Metric)

780.0

Length L (Imperial)

32.3

Length L (Metric)

820.0

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.35

Width W (Metric)

8.8

Bundle Diameter Min (Imperial)

0.32

Bundle Diameter Min (Metric)

8.0

Bundle Diameter Max (Imperial)

9.6

Bundle Diameter Max (Metric)

245.0

Cable Tie Width Max (Imperial)	0.346
Cable Tie Width Max (Metric)	8.8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988