

Specification Sheet

Part Number: RT40R0M4



Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg

Article Number	115-06202
Type	RT40R
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special design offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.• Bent tail ensures a quick and simple installation.
Quantity Per	bag

Product Description

HellermannTyton Releasable Cable Ties feature an extended pawl for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg

Global Part Name

RT40R-PA66-BK

Minimum Tensile Strength (Imperial)

40.0

Minimum Tensile Strength (Metric)

180.0

Length L (Imperial)

8.5

Length L (Metric)

215.9

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.16

Width W (Metric)

4.0

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

51.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988