

Specification Sheet

Part Number: 115-06960



1-Piece Cable Tie/Arrowhead Mount, 9.0" Length, 2.0" Bundle Diameter, PA66, Black, 1,000/pkg

Article Number	115-06960
Type	RT50SFK
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•An all-in-one bundling and fixing solution reduces costs.•High-specification materials and superior design suit the fixing and bundling needs of complex applications.•Releasable to provide quick access to bundles.
Quantity Per	bag

Product Description

One-piece mounting ties offer a complete solution by bundling cables while at the same time providing a mounting solution. This tie features an extended pawl, allowing the user to release the tie for bundle maintenance. Push mount ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description	1-Piece Cable Tie/Arrowhead Mount, 9.0" Length, 2.0" Bundle Diameter, PA66, Black, 1,000/pkg
Global Part Name	RT50SFK-PA66-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.0
Length L (Metric)	225
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	Yes
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.055

Thickness T (Metric)	1.4
Height H (Imperial)	0.24
Height H (Metric)	6
Panel Thickness Min(Imperial)	0.31
Panel Thickness Max(Imperial)	0.03
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.28
Mounting Hole Diameter D (Metric)	6.4 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.26
Mounting Hole Diameter D Max (Imperial)	0.275
Mounting Hole Diameter D Max (Metric)	7.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

1.93