

Specification Sheet

Part Number: DCT110HIRH1



Dual Clamp Tie, 19.20" Long, .25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 500/pkg

Article Number	115-31101
Type	DCT11
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Provides dual separation between bundles to prevent chaffing and abrasion.• 150 lb. tensile strength ensures enough strength for heavy duty applications.• Straps are releasable for increased serviceability.
Quantity Per	bag

Product Description

Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy duty equipment. The unique one-piece design features the dual head centered on the strap.

Short Description	Dual Clamp Tie, 19.20" Long, .25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 500/pkg
Global Part Name	DCT11-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	150.0
Minimum Tensile Strength (Metric)	667.0
Length L (Imperial)	19.2
Length L (Metric)	487.68
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	2.3

Bundle Diameter Max (Metric)	58.0
Height H (Imperial)	0.8
Height H (Metric)	20.32
Mounting Hole Diameter D (Imperial)	0.20
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Max (Metric)	6.2
Stud Diameter (Metric)	M6
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500

Customs Number

3926909988

Content Unit(BMEcat)

bag