

## Specification Sheet

Part Number: RT250R0UVX2



Releasable Cable Tie, Release Tab, 20.3" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Article Number	115-41303
Type	RT250R
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Special extended-pawl design offers a release feature for quick and easy access to wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force even after repeated use.</li><li>• Buckle feature on head allows excess strap to be tucked away after installation.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description**

Releasable Cable Tie, Release Tab, 20.3" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg

**Global Part Name**

RT250R-PA66UV-BK

**Minimum Tensile Strength (Imperial)**

250.0

**Minimum Tensile Strength (Metric)**

1115.0

**Length L (Imperial)**

20.3

**Length L (Metric)**

515.0

**Identification Plate Position**

none

**Releasable Closure**

Yes

**Tie Closure**

plastic pawl

**Variant**

Inside Serrated

**Width W (Imperial)**

0.49

**Width W (Metric)**

12.5

**Bundle Diameter Min (Imperial)**

0.47

**Bundle Diameter Min (Metric)**

12.0

**Bundle Diameter Max (Imperial)**

4.9

**Bundle Diameter Max (Metric)**

125.0

<b>Thickness T (Imperial)</b>	0.075
<b>Thickness T (Metric)</b>	1.9
<b>Cable Tie Head Length (Imperial)</b>	0.88
<b>Cable Tie Head Width (Imperial)</b>	0.79
<b>Material</b>	Polyamide 6.6 UV-resistant (PA66UV)
<b>Material Shortcut</b>	PA66UV
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	25
<b>Package Quantity (Metric)</b>	25

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

12.2