

Specification Sheet

Part Number: RT250I0UVX2



Releasable Cable Tie, Release Tab, 28.7" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Article Number	115-41403
Type	RT250I
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special extended-pawl design offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.• Buckle feature on head allows excess strap to be tucked away after installation.
Quantity Per	bag
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Releasable Cable Tie, Release Tab, 28.7" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Global Part Name

RT250I-PA66UV-BK

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

28.7

Length L (Metric)

730.0

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.5

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric)

12.0

Bundle Diameter Max (Imperial)

8.0

Bundle Diameter Max (Metric)

203.0

Thickness T (Imperial)	0.0837
Thickness T (Metric)	2.2
Cable Tie Head Length (Imperial)	0.88
Cable Tie Head Width (Imperial)	0.79
Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

