

Specification Sheet

Part Number: RT250L0X2



Releasable Cable Tie, Release Tab, 34.7" Long, 250lb Tensile Strength, PA66, Black, 25/pkg

Article Number	115-41500
Type	RT250L
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special extended-pawl design offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.• Buckle feature on head allows excess strap to be tucked away after installation.
Quantity Per	bag

Product Description

HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Releasable Cable Tie, Release Tab, 34.7" Long, 250lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name

RT250L-PA66-BK

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

34.6

Length L (Metric)

880.0

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.5

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric)

12.0

Bundle Diameter Max (Imperial)

10.0

Bundle Diameter Max (Metric)

254.0

Cable Tie Width Max (Imperial)

0.49

Cable Tie Width Max (Metric)

12.5

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 V2

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

UL-ZODZ2.E64139

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

25

Package Quantity (Metric)

25

Customs Number

3926909988

