

Specification Sheet

Part Number: SR255X0HIHSUVX2



Article Number

115-42101

Type

SR255X

Color

Black (BK)

Features & Benefits

- High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.
- Special design offers a release feature for quick and easy access to wire bundles.
- Head design provides high tensile strength with very low insertion force even after repeated use.

Quantity Per

bag

Product Description

HellermannTyton SR255 Series heavy-duty cable ties offer a release feature in the head allowing for easy installation with the use of a cable tie tool. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force.

Short Description	Releasable Cable Tie, 14.6" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg
Global Part Name	SR255X-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	250.0
Minimum Tensile Strength (Metric)	1115.0
Length L (Imperial)	14.6
Length L (Metric)	370.0
Identification Plate Position	none
Releasable Closure	Yes
Width W (Imperial)	0.5
Width W (Metric)	12.6
Bundle Diameter Min (Imperial)	0.51
Bundle Diameter Min (Metric)	13.0
Bundle Diameter Max (Imperial)	3.9
Bundle Diameter Max (Metric)	100.0
Cable Tie Width Max (Imperial)	0.49
Cable Tie Width Max (Metric)	12.5

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	6.25