

Specification Sheet

Part Number: T30R1C2



Article Number

116-03011

Type

T30R

Color

Brown (BN)

Features & Benefits

- Inside serrations allow for strong grip on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

Quantity Per

bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66, Brown, 100/pkg

Global Part Name

T30R-PA66-BN

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

5.8

Length L (Metric)

147.32

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.38

Bundle Diameter Max (Metric)

35.0

Thickness T (Metric)

1.1

| | |
|-----------------|----------------------|
| Material | Polyamide 6.6 (PA66) |
|-----------------|----------------------|

| | |
|--------------------------|------|
| Material Shortcut | PA66 |
|--------------------------|------|

| | |
|--------------------|-------------|
| US MIL SPEC | SAE-AS33671 |
|--------------------|-------------|

MS3367-5-1

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

CAGE Code 53421 UL-ZODZ.E64139

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

| | |
|-----------------------------------|-----|
| Package Quantity(Imperial) | 100 |
|-----------------------------------|-----|

| | |
|----------------------------------|-----|
| Package Quantity (Metric) | 100 |
|----------------------------------|-----|

| | |
|-----------------------|------------|
| Customs Number | 3926909988 |
|-----------------------|------------|

| | |
|------------------------|-----|
| Weight (Metric) | 0.7 |
|------------------------|-----|

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)