

## Specification Sheet

Part Number: T30R10C2



Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66, White, 100/pkg

<b>Article Number</b>	116-03019
<b>Type</b>	T30R
<b>Color</b>	White (WH)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Inside serrations allow for strong grip on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
<b>Short Description</b>	Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66, White, 100/pkg

Global Part Name

T30R-PA66-WH

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

5.8

Length L (Metric)

147.32

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.38

Bundle Diameter Max (Metric)

35.0

Thickness T (Metric)

1.1

<b>Material</b>	Polyamide 6.6 (PA66)
-----------------	----------------------

**Material Shortcut** PA66

<b>US MIL SPEC</b>	MS3367-1-10	<b>Flammability</b>
--------------------	-------------	---------------------

UL 94 V2

**Halogen free**

Yes

**Operating Temperature (Metric)**

-40°F to +185°F (-40°C to +85°C)

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL-ZODZ2.E64139

**UL Recognized (US)**

Yes

**UL Listed (US and Canada)**

Yes

**UL Recognized (US and Canada)**

Yes

**UL Listed (US)**

Yes

<b>Package Quantity(Imperial)</b>	100
-----------------------------------	-----

**Package Quantity (Metric)** 100

<b>Customs Number</b>	3926909988
-----------------------	------------

**Content Unit(BMEcat)** pcs.

**Weight (Metric)**

0.7