

Specification Sheet

Part Number: 117-00012



Stand Off Dual Clamp Tie, 20.10" Long, .31" Stud Dia, PA66HIRHSUV, Black, 250/pkg

Article Number	117-00012
Type	SDCTR312
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Wide strap minimizes pinching of soft hoses and convoluted tubing.• Clamping rails increase circumferential grip on varying bundle diameters.• Locking stud mount pawls allow for easy hand insertion.• Nut or weld nesting counterbore provides flush mounting at the base.
Quantity Per	carton
Product Description	Stand Off Dual Clamp Ties offer the same features as the standard dual clamp tie, with a standoff mount that secures the bundle away from the side of the frame rail. This protects the bundles from bolts and other protrusions.
Short Description	Stand Off Dual Clamp Tie, 20.10" Long, .31" Stud Dia, PA66HIRHSUV, Black, 250/pkg

Global Part Name

SDCTR312-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

100

Minimum Tensile Strength (Metric)

445

Length L (Imperial)

20.1

Length L (Metric)

510.5

Fixation Method

Weld Stud Fixing

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Width W (Imperial)

0.5

Width W (Metric)

12.7

Bundle Diameter Min (Imperial)

0.375

Bundle Diameter Min (Metric)

9.5

Bundle Diameter Max (Imperial)

2.3

Bundle Diameter Max (Metric)

58.4

Height H (Imperial)

1.47

Height H (Metric)

37.30

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	5/16
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988
Content Unit(BMEcat)	pcs.

