

Specification Sheet

Part Number: T50LDH0C2



Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66, Black, 100/pkg

Article Number	117-05400
Type	T50LDH
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• The tie contains a dual locking design to secure two bundles at once.• Head design can also provide spacing between parallel bundles.• Bent tail allows for quick insertion into head.
Quantity Per	bag

Product Description

The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66, Black, 100/pkg

Global Part Name

T50LDH-PA66-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

15.6

Length L (Metric)

395.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.6

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

100.0

Bundle Diameter 1st Loop Max (Imperial)	4.0
Bundle Diameter 1st Loop Max (Metric)	101.6
Bundle Diameter 2nd Loop Max (Imperial)	2.0
Bundle Diameter 2nd Loop Max (Metric)	50.8
Thickness T (Imperial)	0.055
Thickness T (Metric)	1.4
Cable Tie Head Length (Imperial)	0.53
Cable Tie Head Width (Imperial)	0.32
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes

Certification/Specification WEB

UL-ZODZ2.E64139

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

Content Unit(BMEcat)

pcs.