

Specification Sheet

Part Number: 121-73390



Kabelrap tie offers a smooth strap providing secure assembly without damaging cables or hoses.

Curved head design provides full circumferential compression which offers vibration resistance.

Kabelrap Tie, 13.3" Long, 176lb Tensile Strength, PA66HS, Black, 50/pkg

Article Number 121-73390

Type KR8/33

Color Black (BK)

Quantity Per pcs.

Product Description The patented Kabelrap cable tie design offers a smooth strap which is locked into place with a glass fiber reinforced pin. The curved head design provides full circumferential compression around the bundle or harness. Once applied with the required KR6/8 manual tool, the tie offers a secure and vibration resistant assembly.

Short Description Kabelrap Tie, 13.3" Long, 176lb Tensile Strength, PA66HS, Black, 50/pkg

Global Part Name KR8/33-PA66HS-BK

Minimum Tensile Strength (Metric)	785
Length L (Metric)	337.0
Fixation Method	Cable Tie
Identification Plate Position	none
Releasable Closure	No
Tie Closure	fibreglass pin
Variant	Not Serrated
Width W (Metric)	8.0
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	3.39
Bundle Diameter Max (Metric)	86.0
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)