

Specification Sheet

Part Number: 121-83355

Product Image  Kabelrap Tie, 13.3" Long, 176lb Tensile Strength, PA66HS, Natural, 50/pkg

Article Number	121-83355
Type	KR8/33
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Kabelrap tie offers a smooth strap providing secure assembly without damaging cables or hoses.• Curved head design provides full circumferential compression which offers vibration resistance.
Quantity Per	pcs.
Product Description	The patented Kabelrap cable tie design offers a smooth strap which is locked into place with a glass fiber reinforced pin. The curved head design provides full circumferential compression around the bundle or harness. Once applied with the required KR6/8 manual tool, the tie offers a secure and vibration resistant assembly.
Short Description	Kabelrap Tie, 13.3" Long, 176lb Tensile Strength, PA66HS, Natural, 50/pkg
Global Part Name	KR8/33-PA66HS-NA
Minimum Tensile Strength (Imperial)	176.0
Minimum Tensile Strength (Metric)	785.0
Length L (Imperial)	13.3

Length L (Metric) 337.0

Fixation Method Cable Tie

Identification Plate Position none

Releasable Closure No

Tie Closure fibreglass pin

Variant No Serration

Width W (Imperial) 0.32

Width W (Metric) 8.0

Bundle Diameter Min (Imperial) 0.32

Bundle Diameter Min (Metric) 8.0

Bundle Diameter Max (Imperial) 3.4

Bundle Diameter Max (Metric) 86.0

Thickness T (Imperial) 0.091

Thickness T (Metric) 2.3

Cable Tie Head Length (Imperial) 0.31

Cable Tie Head Width (Imperial) 0.46

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	4.43