

Specification Sheet

Part Number: 126-00000



1-Piece Cable Tie & Edge Clip, 8" Long, EC13, Panel Thickness .04"-.12", 50 lbs, PA66HS, Black, 500/bag

Article Number

126-00000

Type

T50SOSEC13E

Color

Black (BK)

Features & Benefits

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
- Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
- Cable tie is outside serrated to reduce bundle chafing.

Quantity Per

bag

Product Description

The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description	1-Piece Cable Tie & Edge Clip, 8" Long, EC13, Panel Thickness .04"-.12", 50 lbs, PA66HS, Black, 500/bag
Global Part Name	T50SOSEC13E-PA66HS-BK
Minimum Tensile Strength (Imperial)	40.0
Minimum Tensile Strength (Metric)	180
Length L (Imperial)	6.0
Length L (Metric)	160.0
Fixation Method	Edge Clips
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.40

Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.35
Height H (Imperial)	0.06
Height H (Metric)	1.35
Panel Thickness Min(Imperial)	0.039
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes

Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.95