

Specification Sheet

Part Number: 126-00005



1-Piece Cable Tie/Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Mtg Hole, PA66HIRHS, Black, 500/bag

Article Number	126-00005
Type	T50SL5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.•Arrowhead style mount provides low insertion and high extraction force.•Arrowhead disc protects against dirt and other impurities.
Quantity Per	bag
Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description	1-Piece Cable Tie/Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Mtg Hole, PA66HIRHS, Black, 500/bag
Global Part Name	T50SL5-PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.5
Length L (Metric)	163
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.3

Bundle Diameter Max (Metric)	34.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Panel Thickness Min(Imperial)	0.031
Panel Thickness Max(Imperial)	0.11
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	2.7
Mounting Hole Diameter D (Imperial)	0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.1 - 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.255
Mounting Hole Diameter D Max (Metric)	6.5
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen free	Yes

Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.6