

Specification Sheet

Part Number: 126-00042



1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66HS, Black, 1000/pkg

| | |
|--------------------------------|---|
| Article Number | 126-00042 |
| Type | T18RWPM |
| Color | Black (BK) |
| Features & Benefits | <ul style="list-style-type: none">•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.•Arrowhead style mount provides low insertion and high extraction force.•Arrowhead disc protects against dirt and other impurities. |
| Quantity Per | bag |
| Product Description | Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications. |

Short Description

1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66HS, Black, 1000/pkg

Global Part Name

T18RWPM-PA66HS-BK

Minimum Tensile Strength (Imperial)

18.0

Minimum Tensile Strength (Metric)

80

Length L (Imperial)

4.5

Length L (Metric)

113.0

Fixation Method

Arrowhead

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.1

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

0.86

| | |
|--|--------------|
| Bundle Diameter Max (Metric) | 22.0 |
| Thickness T (Imperial) | 0.043 |
| Thickness T (Metric) | 1.1 |
| Height H (Imperial) | .23 |
| Height H (Metric) | 5.80 |
| Panel Thickness Min(Imperial) | 0.06 |
| Panel Thickness Max(Imperial) | 0.13 |
| Panel Thickness Min (Metric) | 1.52 |
| Panel Thickness Max (Metric) | 3.2 |
| Mounting Hole Diameter D (Imperial) | 0.19 - 0.22 |
| Mounting Hole Diameter D (Metric) | 4.8 - 5.6 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.19 |
| Mounting Hole Diameter D Max (Imperial) | 0.22 |
| Mounting Hole Diameter D Max (Metric) | 5.6 |
| Disc Diameter(Metric) | 13.2 |
| Disc Diameter (Imperial) | 0.5 |

| | |
|--|--|
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut | PA66HS |
| Flammability | UL 94 V2 |
| Operating Temperature (Metric) | -40°F to +221°F (-40°C to +105°C) |
| ROHS Complaint | Yes |
| Certification/Specification WEB | UL |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity(Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |
| Customs Number | 3926909988 |