

## Specification Sheet

Part Number: 126-00044



1-Piece Cable Tie/Arrowhead Mount, 6"L, 50lb, 0.04"–0.14" Panel Thickness, PA66, Natural, 1000/pkg

Article Number	126-00044
Type	T50SSF
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none"><li>•All-in-one bundling and fastening solution reduces costs and assembly time.</li><li>•The arrowhead design of these ties offers a low insertion force and a high extraction force.</li><li>•High-spec materials and superior design deliver versatility, performance and value.</li></ul>
Quantity Per	bag

### Product Description

One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.

<b>Short Description</b>	1-Piece Cable Tie/Arrowhead Mount, 6"L, 50lb, 0.04"–0.14" Panel Thickness, PA66, Natural, 1000/pkg
<b>Global Part Name</b>	T50SSF-PA66-NA
<b>Minimum Tensile Strength (Imperial)</b>	50.0
<b>Minimum Tensile Strength (Metric)</b>	225
<b>Length L (Imperial)</b>	6.25
<b>Length L (Metric)</b>	159.0
<b>Fixation Method</b>	Arrowhead
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.19
<b>Width W (Metric)</b>	4.7
<b>Bundle Diameter Min (Imperial)</b>	0.06
<b>Bundle Diameter Min (Metric)</b>	1.5
<b>Bundle Diameter Max (Imperial)</b>	1.4

<b>Bundle Diameter Max (Metric)</b>	35.0
<b>Height H (Imperial)</b>	.30
<b>Height H (Metric)</b>	7.50
<b>Panel Thickness Min(Imperial)</b>	0.039
<b>Panel Thickness Max(Imperial)</b>	0.14
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.56
<b>Mounting Hole Diameter D (Imperial)</b>	0.25 " - 0.28
<b>Mounting Hole Diameter D (Metric)</b>	6.4 - 7.1 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.25
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.28
<b>Mounting Hole Diameter D Max (Metric)</b>	7.1
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)

<b>ROHS Complaint</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988