

## Specification Sheet

Part Number: 126-00049



1-Piece Cable Tie/Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Mtg Hole, PA66HIRHS, Black, 500/bag

<b>Article Number</b>	126-00049
<b>Type</b>	T50SSFM
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.</li><li>•Arrowhead style mount provides low insertion and high extraction force.</li><li>•Arrowhead disc protects against dirt and other impurities.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

<b>Short Description</b>	1-Piece Cable Tie/Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Mtg Hole, PA66HIRHS, Black, 500/bag
<b>Global Part Name</b>	T50SSFM-PA66HIRHS-BK
<b>Minimum Tensile Strength (Imperial)</b>	50.0
<b>Minimum Tensile Strength (Metric)</b>	225
<b>Length L (Imperial)</b>	6.3
<b>Length L (Metric)</b>	160.0
<b>Fixation Method</b>	Arrowhead
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.18
<b>Width W (Metric)</b>	4.6
<b>Bundle Diameter Min (Imperial)</b>	0.06
<b>Bundle Diameter Min (Metric)</b>	1.5
<b>Bundle Diameter Max (Imperial)</b>	1.4

<b>Bundle Diameter Max (Metric)</b>	35.0
<b>Height H (Imperial)</b>	.20
<b>Height H (Metric)</b>	5.60
<b>Panel Thickness Min(Imperial)</b>	0.028
<b>Panel Thickness Max(Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	0.7
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.24 - 0.26
<b>Mounting Hole Diameter D (Metric)</b>	6.0 - 6.6 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.24
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.25
<b>Mounting Hole Diameter D Max (Metric)</b>	6.6
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Shortcut</b>	PA66HIRHS
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.