

## Specification Sheet

Part Number: 126-00079



1-Piece Cable Tie/Fir Tree Mount, 6.2" Long, Mounting Hole Diameter .28"-.47", PA66HS, Black, 500/pkg

**Article Number**

126-00079

**Type**

T60SOSSFT70x120-E-MD

**Color**

Black (BK)

**Features & Benefits**

- Design helps silence and stabilize the tie in high-vibration applications.
- Arrowhead-style mount provides low insertion and high extraction force.
- Anti-rotational oval fastener forces bundle to travel in intended direction.
- Rubber seal restricts water and debris from passing through mounting hole.

**Quantity Per**

bag

**Product Description**

Push Mount Ties with Seal for Oval Holes provide a one-piece bundling and mounting solution. The oval arrowhead fastener won't rotate once inserted into a panel hole, ensuring proper routing of wires and hoses. The welded rubber seal protects against the ingress of water and debris.

<b>Short Description</b>	1-Piece Cable Tie/Fir Tree Mount, 6.2" Long, Mounting Hole Diameter .28"-.47", PA66HS, Black, 500/pkg
<b>Global Part Name</b>	T60SOSSFT70x120-E-MD-PA66HS-BK
<b>Minimum Tensile Strength (Imperial)</b>	67.0
<b>Minimum Tensile Strength (Metric)</b>	300
<b>Length L (Imperial)</b>	6.2
<b>Length L (Metric)</b>	157.7
<b>Fixation Method</b>	Arrowhead for oval holes
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Outside Serrated
<b>Width W (Imperial)</b>	0.22
<b>Width W (Metric)</b>	5.5
<b>Bundle Diameter Min (Imperial)</b>	0.06
<b>Bundle Diameter Min (Metric)</b>	1.6
<b>Bundle Diameter Max (Imperial)</b>	1.18

<b>Bundle Diameter Max (Metric)</b>	30.0
<b>Thickness T (Metric)</b>	1.35
<b>Panel Thickness Min(Imperial)</b>	0.028
<b>Panel Thickness Max(Imperial)</b>	0.079
<b>Panel Thickness Min (Metric)</b>	0.6
<b>Panel Thickness Max (Metric)</b>	2.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.28 - 0.47
<b>Mounting Hole Diameter D (Metric)</b>	7.0 x 12.0 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.28
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.47
<b>Mounting Hole Diameter D Max (Metric)</b>	12.0
<b>Disc Diameter(Metric)</b>	16.0 x 22.0
<b>Disc Diameter (Imperial)</b>	0.63
<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HS
<b>Flammability</b>	UL 94 V2

**Operating Temperature (Metric)** -40°F to +221°F (-40°C to +105°C)

**Reach Complaint(Article 33)** Yes

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 500

**Package Quantity (Metric)** 500

**Customs Number** 3926909988

**Content Unit(BMEcat)** pcs.

**Weight (Metric)** 2.05