

## Specification Sheet

Part Number: 126-00081



1-Piece Cable Tie/Arrowhead Mount, 6"L, 50lb Tensile Strength, 6.5mm Round Hole, PA66HS Black, 500/pkg

<b>Article Number</b>	126-00081
<b>Type</b>	T50SOSKSFT6.5E
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•All-in-one bundling and mounting solution reduces costs.</li><li>•Low-profile design provides dependable cable management in tight spaces.</li></ul>
<b>Quantity Per</b>	bag

### Product Description

The low-profile push mount design provides an overall shortened length, which assists in limiting protrusion on the opposing side of application surfaces. The mount's rounded tip allows for a smoother surface in case of contact with surrounding components or hands. The dome provides firm, rattle-free performance and keeps out debris. One-piece mounting ties offer a complete solution by both bundling and mounting.

<b>Short Description</b>	1-Piece Cable Tie/Arrowhead Mount, 6"L, 50lb Tensile Strength, 6.5mm Round Hole, PA66HS Black, 500/pkg
<b>Global Part Name</b>	T50SOSKSFT6.5E-PA66HS-BK
<b>Minimum Tensile Strength (Imperial)</b>	40.0
<b>Minimum Tensile Strength (Metric)</b>	180.0
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	156.0
<b>Fixation Method</b>	Arrowhead (Small Mount)
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Outside Serrated
<b>Width W (Imperial)</b>	0.18
<b>Width W (Metric)</b>	4.6
<b>Bundle Diameter Min (Imperial)</b>	0.04
<b>Bundle Diameter Min (Metric)</b>	1.0
<b>Bundle Diameter Max (Imperial)</b>	1.4

<b>Bundle Diameter Max (Metric)</b>	35.0
<b>Panel Thickness Min(Imperial)</b>	0.03
<b>Panel Thickness Max(Imperial)</b>	0.05
<b>Panel Thickness Min (Metric)</b>	0.7
<b>Panel Thickness Max (Metric)</b>	1.3
<b>Mounting Hole Diameter D (Imperial)</b>	0.25 - 0.26
<b>Mounting Hole Diameter D (Metric)</b>	6.3 - 6.7 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.25
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.26
<b>Mounting Hole Diameter D Max (Metric)</b>	6.7
<b>Disc Diameter(Metric)</b>	16.0
<b>Disc Diameter (Imperial)</b>	0.63
<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HS
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C)

<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.
<b>Weight (Metric)</b>	1.3