

Specification Sheet

Part Number: 126-00114



1-Piece Cable Tie/Arrowhead Mount, 8.5"L, 50lb, Panel Thickness .07"-.12", PA66HIRHS, Natural, 500/pkg

Article Number	126-00114
Type	T50ROSAH6U
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•An all-in-one bundling and fixing solution reduces costs.•Disc provides secure insertion and minimizes access of dust, dirt and water.
Quantity Per	bag
Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	1-Piece Cable Tie/Arrowhead Mount, 8.5"L, 50lb, Panel Thickness .07"-.12", PA66HIRHS, Natural, 500/pkg

Global Part Name

T50ROSAH6U-PA66HIRHS-NA

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

8.5

Length L (Metric)

215.9

Fixation Method

Arrowhead

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.20

Width W (Metric)

5.0

Bundle Diameter Min (Imperial)

0.04

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.0

Panel Thickness Min(Imperial)

0.07

Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.8
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter(Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.