

Specification Sheet

Part Number: GTM100A0C2



Grip Tie Mount for .75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg

Article Number	130-91001
Type	GTM100A
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Adhesive with 1/4" screw hole mount secures .75" grip ties for use on flat surfaces
Quantity Per	bag
Product Description	To secure bundles to flat surfaces, HellermannTyton offers a mounting base to be used with the Grip Ties. Available with or without adhesive, two sizes of Grip Tie mounts cover every size of Grip Tie. The mounts are manufactured from nylon 6/6 material and are UV-stabilized for outdoor applications.
Short Description	Grip Tie Mount for .75" Wide Grip Tie, Adhesive, PA66UV, Black, 100/pkg

Global Part Name

GTM100A-PA66UV-BK

Length L (Imperial)

3.25

Length L (Metric)

82.55

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

hook and loop

Variant

Grip Tie

Width W (Imperial)

1.5

Width W (Metric)

38.1

Bolt Size

1/4" (M6) Screw

Material

Polyamide 6.6 UV-resistant (PA66UV)

Material Shortcut

PA66UV

Adhesive

Urethane foam

ROHS Complaint

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988