

Specification Sheet

Part Number: RT250L9X2



Releasable Cable Tie, Release Tab, 34.7" Long, 250lb Tensile Strength, PA66, Natural, 25/pkg

Article Number	131-75419
Type	RT250L
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Special extended-pawl design offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.• Buckle feature on head allows excess strap to be tucked away after installation.
Quantity Per	bag

Product Description

HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Releasable Cable Tie, Release Tab, 34.7" Long, 250lb Tensile Strength, PA66, Natural, 25/pkg
Global Part Name	RT250L-PA66-NA
Minimum Tensile Strength (Imperial)	250.0
Minimum Tensile Strength (Metric)	1115.0
Length L (Imperial)	34.6
Length L (Metric)	880.0
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.49
Width W (Metric)	12.5
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	10.0
Bundle Diameter Max (Metric)	254.0

Thickness T (Imperial)	0.0837
Thickness T (Metric)	2.2
Cable Tie Head Length (Imperial)	0.88
Cable Tie Head Width (Imperial)	0.79
Cable Tie Width Max (Imperial)	0.49
Cable Tie Width Max (Metric)	12.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity(Imperial)

25

Package Quantity (Metric)

25

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

29