

Specification Sheet

Part Number: RT250XL0X2



Releasable Cable Tie, Release Tab, 40.6" Long, 250lb Tensile Strength, PA66, Black, 25/pkg

Article Number	131-75510
Type	RT250XL
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special extended-pawl design offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.• Buckle feature on head allows excess strap to be tucked away after installation.
Quantity Per	bag
Product Description	HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Releasable Cable Tie, Release Tab, 40.6" Long, 250lb Tensile Strength, PA66, Black, 25/pkg
Global Part Name	RT250XL-PA66-BK
Minimum Tensile Strength (Imperial)	250.0
Minimum Tensile Strength (Metric)	1115.0
Length L (Imperial)	40.6
Length L (Metric)	1030.0
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.49
Width W (Metric)	12.5
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	12.0
Bundle Diameter Max (Metric)	305.0

Thickness T (Imperial)	0.0837
Thickness T (Metric)	2.2
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 62275 UL ANSI/UL 746B UL ANSI/UL 1565
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Content Unit(BMEcat)	pcs.

