

Specification Sheet

Part Number: 133-01497



Clip can be installed by hand – no need for hardware or tools. Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.73" Long, Panel Thickness 0.02–0.27", PA66HIRHS, Natural, 2000/carton

Article Number 133-01497

Type SOC14FT6

Color Natural (NA)

Quantity Per box

Product Description Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Short Description Standoff Bundling Clip, 1.73" Long, Panel Thickness 0.02–0.27", PA66HIRHS, Natural, 2000/carton

Global Part Name SOC14FT6-PA66HIRHS-NA

Length L (Imperial) 1.77

Length L (Metric) 45.0

Offset Length (Imperial) 0.80

Offset Length (Metric) 20.3

Fixation Method Fir Tree

Panel Thickness Min (Imperial) 0.02

Panel Thickness Max (Imperial) 0.24

Panel Thickness Min (Metric) 0.6

Panel Thickness Max (Metric) 6.0

Mounting Hole Diameter D (Imperial) 0.24 - 0.27

Mounting Hole Diameter D (Metric) 6.1 - 6.9 mm

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.27

Mounting Hole Diameter D Max (Metric) 6.9

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)