

## Specification Sheet

Part Number: 133-04335

Bundling clip allows for routing of a bundle through high heat areas. Made from Flexible PPS high heat material for exceptional heat and chemical resistance.



6.5x12.5 portable oval hole allows the routing to be secured away from obstructions and sources of heat and or abrasion

Dog bone ends help keep bundling clip from slipping off routing.

Bundling Clip with arrowhead, 90 DEG offset, 12.35mm hole dia., 13.5-15.0mm thickness, PPS, Silver, 2500/ctn

|                     |   |
|---------------------|---|
| Article Number      | 133-04335   |
| Type                | BCATC90DEG  |
| Color               | Silver (SR)   |
| Quantity Per        | bag   |
| Product Description | HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location. |
| Short Description   | Bundling Clip with arrowhead, 90 DEG offset, 12.35mm hole dia., 13.5-15.0mm thickness, PPS, Silver, 2500/ctn              |
| Global Part Name    | BCATC90DEG-PPS-SR   |

|   |                |
|---|----------------|
| Length L (Imperial)                     | 2.0            |
| Length L (Metric)                       | 51.0           |
| Offset Length (Imperial)                | 1.47           |
| Offset Length (Metric)                  | 37.5           |
| Fixation Method                         | Arrowhead      |
| Width W (Imperial)                      | 0.62           |
| Width W (Metric)                        | 16.0           |
| Height H (Imperial)                     | 2.0            |
| Height H (Metric)                       | 51.0           |
| Panel Thickness Min (Imperial)          | 0.53           |
| Panel Thickness Max (Imperial)          | 0.59           |
| Panel Thickness Min (Metric)            | 13.5           |
| Panel Thickness Max (Metric)            | 15.0           |
| Mounting Hole Diameter D (Imperial)     | 0.46 - 0.51    |
| Mounting Hole Diameter D (Metric)       | 11.7 - 13.0 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.46           |

Mounting Hole Diameter D Max (Imperial) 0.51

Mounting Hole Diameter D Max (Metric) 13.0

Material Polyphenylene Sulfide (PPS)

Material Shortcut PPS

UV Resistant (Yes/No) No

Reach Compliant (Article 33) No

Package Quantity (Imperial) 2500

Package Quantity (Metric) 2500

Customs Number 3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)