

Specification Sheet

Part Number: 148-00092



Wire Clamping Cable Ties, Version A, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

| | |
|---------------------|--|
| Article Number | 148-00092 |
| Type | T50SOSWA4.3E |
| Color | Black (BK) |
| Features & Benefits | <ul style="list-style-type: none">• Clamp provides low insertion and high extraction force.• Various sizes available to accommodate all different sizes of bundles.• Clamp can be installed both before and after installation of bundles. |
| Quantity Per | bag |

Product Description

Wire Clamping Cable Ties secure easily to wire frames for a tight fit and are available in four different wire frame sizes and two separate orientations to provide both perpendicular and parallel routing. The wire clamp design is ideally suited for easing the application process on the production floor by allowing for an easy snap fit of the harness assembly to the wire frame.

Short Description

Wire Clamping Cable Ties, Version A, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

Global Part Name

T50SOSWA4.3E-PA66HS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

6.0

Length L (Metric)

150.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Width W (Imperial)

0.18

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.6

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.0

Thickness T (Imperial)

0.05

| | |
|---------------------------------------|--|
| Thickness T (Metric) | 1.3 |
| Diameter D (imperial) | 0.17 |
| Nominal Diameter (Imperial) | 3/16 |
| Nominal Diameter (Metric) | 4.3 |
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut | PA66HS |
| Operating Temperature (Metric) | -40°F to +221°F (-40°C to +105°C) |
| Reach Complaint(Article 33) | Yes |
| ROHS Complaint | Yes |
| Package Quantity(Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |
| Content Unit(BMEcat) | pcs. |

