

Specification Sheet

Part Number: 148-90050



HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 4-Port, (PC), Clear, 300/pkg

Article Number

148-90050

Type

HCPM-4

Color

Clear (CL)

Features & Benefits

- Spring technology for safe, secure and reliable connections.
- Smaller footprint fits in tight spaces.
- Low insertion force makes installation of solid or stranded copper wire fast and easy.
- Color coded for easy identification of size.
- Each port accepts multiple wire diameters for flexible applications.
- Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.

Quantity Per

pack

Product Description

HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal spring technology is approved for solid and stranded wires.

Short Description

HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 4-Port, (PC), Clear, 300/pkg

Global Part Name

HCPM-4-PC-CL

Length L (Imperial)

0.65

Length L (Metric)

16.5

Width W (Imperial)

0.76

Width W (Metric)

19.4

Height H (Imperial)

0.30

Height H (Metric)

7.70

Depth D (imperial)

0.65

Depth D (metric)

16.5

Material

Polycarbonate (PC)

Material Shortcut

PC

Flammability

UL 94 V0

Halogen free

Yes

Operating Temperature (Metric)

-22°F to +185°F (-30°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

UL | ANSI/UL 486-B UL | ANSI/UL 486-C Intertek Semko | EN 60998-2-2:2004
cULus NEMKO AS | EN 60998-2-2:2004 SGS Fimko Ltd | EN 60998-2-2:201
CE | 2006/65/EC SGS Fimko Ltd | EN 60998-2-2:2004 ENEC UL | ANSI/UL
486-A

UL Listed (US and Canada)

Yes

UL Listed (US

Yes

Package Quantity(Imperial)

300

Package Quantity (Metric)

300

Customs Number

8536695050