

## Specification Sheet

Part Number: 150-28140



Ladder Stud Mount, 4.3" Length, Stud Diameter .2", Max Bundle Diameter 0.91", PA66, Black, 500/pkg

<b>Article Number</b>	150-28140
<b>Type</b>	FBB140
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Mount design applies quickly and easily to .2" (5mm) studs.</li><li>• Unique latch style allows for easy re-entry to bundles.</li><li>• Design gives low insertion force and high extraction force.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Ladder Stud Mounts can be used in a wide variety of applications where .2" diameter bolts are used, and cables need to be bundled and secured. The unique latch style allows for easy re-entry to bundles.
<b>Short Description</b>	Ladder Stud Mount, 4.3" Length, Stud Diameter .2", Max Bundle Diameter 0.91", PA66, Black, 500/pkg

Global Part Name

FBB140-PA66-BK

Length L (Imperial)

5.7

Length L (Metric)

142

Fixation Method

Weld Stud Fixing

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

ladder style

Variant

No Serration

Width W (Imperial)

0.4

Width W (Metric)

10.0

Bundle Diameter Min (Imperial)

0.24

Bundle Diameter Min (Metric)

6.0

Bundle Diameter Max (Imperial)

1.5

Bundle Diameter Max (Metric)

38.0

Height H (Imperial)

0.06

Height H (Metric)

1.4

Stud Diameter (Metric)

5.0 mm

<b>Stud Diameter (Imperial)</b>	0.2
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.
<b>Weight (Metric)</b>	1.86

