

Specification Sheet

Part Number: 150-37791



2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bag

Article Number

150-37791

Type

T50ROSSFT6.5 16-3

Color

Black (BK)

Features & Benefits

- Two-piece assembly allows mount to slide along strap, ensuring proper orientation.
- Arrowhead-style mount provides low insertion and high extraction force.
- Multiple material options provide solutions for any environment.

Quantity Per

bag

Product Description

HellermannTyton's Arrowhead Push Mount Tie Assembly is a two piece design allowing the mount to slide along the strap of the tie to ensure proper orientation. The arrowhead mount is designed for low insertion into a pre-drilled hole, while providing a high extraction force. The disc also protects against dirt and other impurities.

Short Description

2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bag

Global Part Name

T50ROSSFT6.5 16-3-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

7.87

Length L (Metric)

200

Fixation Method

Arrowhead

Identification Plate Position

none

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.181

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.197

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

1.77

Bundle Diameter Max (Metric)

45.0

Height H (Imperial)	0.051
Height H (Metric)	1.3
Panel Thickness Min(Imperial)	0.098
Panel Thickness Max(Imperial)	0.138
Panel Thickness Min (Metric)	2.5
Panel Thickness Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.248 - 0.264
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.248
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter(Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS

Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.9