

Specification Sheet

Part Number: 150-55610



1-Piece Cable Tie/Fir Tree Mount with Disc, 4.3"L, .19"-.20" Mounting Hole, PA66, Black, 500/pkg

Article Number	150-55610
Type	T18RDP5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Fir tree mounts are equipped with a friction tab that will hold the tie in the mount, allowing them to be preassembled prior to installation.• Fir Tree design provides low extraction and high extraction force.
Quantity Per	pcs.
Product Description	Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. This is sold as an assembly with the cable tie.
Short Description	1-Piece Cable Tie/Fir Tree Mount with Disc, 4.3"L, .19"-.20" Mounting Hole, PA66, Black, 500/pkg

Global Part Name

T18RDP5-PA66-BK

Minimum Tensile Strength (Imperial)

18.0

Minimum Tensile Strength (Metric)

80

Length L (Imperial)

4.3

Length L (Metric)

110.0

Fixation Method

Fir Tree

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.1

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

0.8

Bundle Diameter Max (Metric)

20.0

Thickness T (Imperial)

0.043

Thickness T (Metric)	1.1
Panel Thickness Min(Imperial)	0.12
Panel Thickness Max(Imperial)	0.02
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	4.0
Mounting Hole Diameter D (Imperial)	0.19 - 0.2
Mounting Hole Diameter D (Metric)	4.9 - 5.1 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.197
Mounting Hole Diameter D Max (Metric)	5.1
Disc Diameter(Metric)	13.0
Disc Diameter (Imperial)	0.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.6