

Specification Sheet

Part Number: 150-55948



2-Piece Cable Tie/Fir Tree Mount, 6.0"L, .17"-.20" Mounting Hole Diameter, PA46, Grey, 500/pkg

Article Number	150-55948
Type	T30RFT5
Color	Natural (NA) Gray (GY)
Features & Benefits	<ul style="list-style-type: none">•Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.•Fir tree provides low insertion effort yet demonstrates high extraction resistance.•Disc feature prevents rattling in high-vibration applications and protects against debris ingress.
Quantity Per	bag
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description	2-Piece Cable Tie/Fir Tree Mount, 6.0"L, .17"-.20" Mounting Hole Diameter, PA46, Grey, 500/pkg
Global Part Name	T30RFT5-PA46-NA/GY
Minimum Tensile Strength (Imperial)	30.0
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	6.0
Length L (Metric)	150.0
Fixation Method	Fir Tree
Identification Plate Position	none
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14
Width W (Metric)	3.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.4
Bundle Diameter Max (Metric)	34.0

Thickness T (Imperial)	0.043
Thickness T (Metric)	1.1
Height H (Imperial)	0.04
Height H (Metric)	1.2
Panel Thickness Min(Imperial)	0.03
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.17 - 0.2
Mounting Hole Diameter D (Metric)	4.5 - 5.0 mm
Mounting Hole Diameter D Min (Imperial)	0.177
Mounting Hole Diameter D Max (Imperial)	0.197
Mounting Hole Diameter D Max (Metric)	5.0
Disc Diameter(Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 4.6 (PA46)

Material Shortcut PA46

Material Cable Tie Polyamide 4.6 (PA46)

Flammability UL 94 V2

Operating Temperature (Metric) -40°F to +302°F (-40°C to +150°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Package Quantity(Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

Content Unit(BMEcat) pcs.

Weight (Metric) 1.2