

Specification Sheet

Part Number: MMB.50C2



Masonry Cable Tie Mount, 1.24"L, .25" Hole Dia, .18" Max Cable Tie Width, PA66STHS, BK, 100/pkg

Article Number	151-00116
Type	MMB.5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Masonry Mounts provide a permanent solution when fastening wire and cables to masonry surfaces.•The mounts have easy installation into predrilled holes allowing for faster use.
Quantity Per	bag
Product Description	HellermannTyton Masonry Mounts provide a permanent method of attaching wire and cable to masonry surfaces. Masonry mounts simply tap into predrilled holes and can be used for indoor and outdoor applications.
Short Description	Masonry Cable Tie Mount, 1.24"L, .25" Hole Dia, .18" Max Cable Tie Width, PA66STHS, BK, 100/pkg

Global Part Name

MMB.5-PA66STHS-BK

Length L (Imperial)

1.24

Length L (Metric)

31.5

Fixation Method

with Fir Tree (Mounts)

Width W (Imperial)

0.375

Width W (Metric)

9.5

Cable Ties

T18 - T50

Height H (Imperial)

.37

Height H (Metric)

9.40

Cable Tie Width Max (Imperial)

0.18

Cable Tie Width Max (Metric)

4.6

Mounting Hole Diameter D (Imperial)

0.25

Mounting Hole Diameter D (Metric)

6.35 mm

Mounting Hole Diameter D Max (Metric)

6.35

Material

Polyamide 6.6, Super Tough, Heat Stabilized (PA66STHS)

Material Shortcut PA66STHS

Flammability UL 94 HB

Operating Temperature (Metric) -40°F to +221°F (-40°C to +105°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Package Quantity(Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

Content Unit(BMEcat) pcs.