

Specification Sheet

Part Number: 151-00180



Connector Clip w/Oval Fir Tree, 0.6 - 6.0 mm Panel Thickness, 6.2 x 12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg

Article Number	151-00180
Type	YCCFT62x122
Color	Black (BK)
Features & Benefits	•Head design contains clamping rails to provide full circumferential compression around bundles. •Bent tail allows for quick insertion into head.
Quantity Per	pcs.

Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description	Connector Clip w/Oval Fir Tree, 0.6 - 6.0 mm Panel Thickness, 6.2 x 12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg
Global Part Name	YCCFT62x122-PA66HIRHS-BK
Length L (Imperial)	0.83
Length L (Metric)	21.08
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.63
Width W (Metric)	16.0
Height H (Imperial)	0.71
Height H (Metric)	18.0
Panel Thickness Min(Imperial)	0.02
Panel Thickness Max(Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.244

Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.18

