

## Specification Sheet

Part Number: MB19C2



Cable Tie Anchor Mount, .50" x .312" .13" Hole Dia, .1" Max Tie Width, PA66, Natural, 100/pkg

<b>Article Number</b>	151-00226
<b>Type</b>	MB1
<b>Color</b>	Natural (NA)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Compact size for areas with limited mounting space.</li><li>•Simple to install with a screw or rivet.</li><li>•Single hole attachment with two-way entry for cable tie.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	These cable tie mounts are compact in size. They are designed for simple yet robust installation particularly in areas with limited space. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.
<b>Short Description</b>	Cable Tie Anchor Mount, .50" x .312" .13" Hole Dia, .1" Max Tie Width, PA66, Natural, 100/pkg

**Global Part Name**

MB1-PA66-NA

**Length L (Imperial)**

0.5

**Length L (Metric)**

12.7

**Fixation Method**

Screw Mounting and Rivet

**Width W (Imperial)**

0.312

**Width W (Metric)**

7.92

**Cable Ties**

T18

**Height H (Imperial)**

.13

**Height H (Metric)**

3.30

**Cable Tie Width Max (Imperial)**

0.1

**Cable Tie Width Max (Metric)**

2.54

**Mounting Hole Diameter D (Imperial)**

0.13

**Mounting Hole Diameter D (Metric)**

3.3 mm

**Mounting Hole Diameter D Max (Metric)**

3.3

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Flammability**

UL 94 V2

**Halogen free**

Yes

**Operating Temperature (Metric)**

-40°F to +185°F (-40°C to +85°C)

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

100

**Package Quantity (Metric)**

100

**Customs Number**

3926909988