

## Specification Sheet

Part Number: PBM0C2



Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, Black, 100/pkg

<b>Article Number</b>	151-00228
<b>Type</b>	PBM
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.</li><li>• The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.
<b>Short Description</b>	Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, Black, 100/pkg

Global Part Name

PBM-PA66-BK

Width W (Imperial)

0.26

Width W (Metric)

6.6

Cable Ties

T18 - T50

Height H (Imperial)

.40

Height H (Metric)

10.20

Cable Tie Width Max (Imperial)

0.2

Cable Tie Width Max (Metric)

5.0

Panel Thickness Max(Imperial)

0.12

Panel Thickness Max (Metric)

3.0

Mounting Hole Diameter D (Imperial)

0.25 - 0.29

Mounting Hole Diameter D (Metric)

6.25 - 6.55 mm

Mounting Hole Diameter D Min (Imperial)

0.25

Mounting Hole Diameter D Max (Imperial)

0.29

Mounting Hole Diameter D Max (Metric)

6.55

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988