

Specification Sheet

Part Number: PBM10C2



Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg

Article Number	151-00230
Type	PBM
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.• The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.
Quantity Per	bag
Product Description	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.
Short Description	Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg

Global Part Name

PBM-PA66-WH

Width W (Imperial)

0.26

Width W (Metric)

6.6

Cable Ties

T18 - T50

Height H (Imperial)

.40

Height H (Metric)

10.20

Cable Tie Width Max (Imperial)

0.2

Cable Tie Width Max (Metric)

5.0

Panel Thickness Max(Imperial)

0.12

Panel Thickness Max (Metric)

3.0

Mounting Hole Diameter D (Imperial)

0.25 - 0.29

Mounting Hole Diameter D (Metric)

6.25 - 6.55 mm

Mounting Hole Diameter D Min (Imperial)

0.25

Mounting Hole Diameter D Max (Imperial)

0.29

Mounting Hole Diameter D Max (Metric)

6.55

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988