


## Specification Sheet

Part Number: IMP2.5W1.7510H4



**Article Number**

151-00242

**Type**

IMP2.5W1.75

**Color**

White (WH)

### Features & Benefits

- Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of labeling options.
- Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected, provided the cable tie width does not exceed .29".
- The marker plates are stamped from nylon, making them a durable and long term method of identification.
- The mounting holes are positioned to allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide variety of installed positions.

**Quantity Per**

bag

### Product Description

Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

<b>Short Description</b>	Identification Marker Plate, 2.5" x 1.75", Nylon, White, 500/pkg
<b>Global Part Name</b>	IMP2.5W1.75-PA66-WH
<b>Fixation Method</b>	Others
<b>Identification Plate Position</b>	attached to bundle
<b>Variant</b>	Other
<b>Width W (Imperial)</b>	2.5
<b>Width W (Metric)</b>	63.5
<b>Height H (Imperial)</b>	1.75
<b>Height H (Metric)</b>	44.45
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Complaint(Article 33)</b>	No

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988