

Specification Sheet

Part Number: SRCI0750C2



TSR Adhesive Cable Clamp, 1.25" Width, .77" Height, PVC, Ivory, 100/pkg

Article Number	151-00279
Type	SRCI0750
Color	Ivory (IV)
Features & Benefits	<ul style="list-style-type: none">• Co-extruded hinge offers unlimited access to wire and cables and can be open and closed repeatedly without signs of wear.• Rubber based adhesive allows for a permanent bond to most surfaces.
Quantity Per	bag
Product Description	Manufactured from HellermannTyton's surface raceway, these adhesive cable clamps are designed with a co-extruded hinge offering unlimited and easy access to wire and cable. The clip can be open and closed repeatedly without deformation or signs of wear. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.
Short Description	TSR Adhesive Cable Clamp, 1.25" Width, .77" Height, PVC, Ivory, 100/pkg

Global Part Name

SRCI0750-PVC-BGE

Length L (Imperial)

1.25

Length L (Metric)

31.75

Width W (Imperial)

1.36

Width W (Metric)

34.5

Bundle Diameter Max (Imperial)

0.75

Bundle Diameter Max (Metric)

19.0

Height H (Imperial)

.77

Height H (Metric)

19.60

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Adhesive

Rubber

Flammability

UL 94 V0 (excluding adhesive)

Operating Temperature (Metric)

+122°F (+50°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988