

Specification Sheet

Part Number: SRCI1000K2



TSR Adhesive Cable Clamp, 1.74" Width, 1" Height, PVC, Ivory, 100/pkg

| | |
|--------------------------------|---|
| Article Number | 151-00280 |
| Type | SRCI1000 |
| Color | Ivory (IV) |
| Features & Benefits | <ul style="list-style-type: none">• Co-extruded hinge offers unlimited access to wire and cables and can be open and closed repeatedly without signs of wear.• Rubber based adhesive allows for a permanent bond to most surfaces. |
| Quantity Per | bag |
| Product Description | Manufactured from HellermannTyton's surface raceway, these adhesive cable clamps are designed with a co-extruded hinge offering unlimited and easy access to wire and cable. The clip can be open and closed repeatedly without deformation or signs of wear. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes. |
| Short Description | TSR Adhesive Cable Clamp, 1.74" Width, 1" Height, PVC, Ivory, 100/pkg |

Global Part Name

SRCI1000-PVC-BGE

Length L (Imperial)

1.75

Length L (Metric)

44.45

Width W (Imperial)

1.88

Width W (Metric)

47.8

Bundle Diameter Max (Imperial)

1.0

Bundle Diameter Max (Metric)

25.4

Height H (Imperial)

1.0

Height H (Metric)

25.40

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Adhesive

Rubber

Flammability

UL 94 V0 (excluding adhesive)

Operating Temperature (Metric)

+122°F (+50°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988