

Specification Sheet

Part Number: MB29M4



Cable Tie Anchor Mount, .81" x .49", .193" Hole Dia, .18" Max Tie Width, PA66, Natural, 1000/pkg

Article Number	151-00297
Type	MB2
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Compact size for areas with limited mounting space.•Simple to install with a screw or rivet.•Single hole attachment with two-way entry for cable tie.
Quantity Per	bag
Product Description	These cable tie mounts are compact in size. They are designed for simple yet robust installation particularly in areas with limited space. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.
Short Description	Cable Tie Anchor Mount, .81" x .49", .193" Hole Dia, .18" Max Tie Width, PA66, Natural, 1000/pkg

Global Part Name

MB2-PA66-NA

Length L (Imperial)

0.81

Length L (Metric)

20.6

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

0.49

Width W (Metric)

12.5

Cable Ties

T18 - T50

Height H (Imperial)

.13

Height H (Metric)

3.30

Cable Tie Width Max (Imperial)

0.18

Cable Tie Width Max (Metric)

4.6

Mounting Hole Diameter D (Imperial)

0.193

Mounting Hole Diameter D (Metric)

4.9 mm

Mounting Hole Diameter D Max (Metric)

4.9

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988