

## Specification Sheet

Part Number: MB40C2



**Article Number**

151-00320

**Type**

MB4

**Color**

Black (BK)

**Features & Benefits**

- Compact size fits most mounting applications.
- Simple to install with a screw or rivet.
- Single hole attachment with two-way entry for cable tie.

**Quantity Per**

bag

**Product Description**

These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

**Short Description**

Screw Mount Cable Tie Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66, Black, 100/pkg

**Global Part Name**

MB4-PA66-BK

<b>Length L (Imperial)</b>	1.12
<b>Length L (Metric)</b>	28.5
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	1.12
<b>Width W (Metric)</b>	28.5
<b>Cable Ties</b>	T18 - 50
<b>Height H (Imperial)</b>	.19
<b>Height H (Metric)</b>	4.80
<b>Cable Tie Width Max (Imperial)</b>	0.18
<b>Cable Tie Width Max (Metric)</b>	4.6
<b>Mounting Hole Diameter D (Imperial)</b>	0.18
<b>Mounting Hole Diameter D (Metric)</b>	4.6 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	4.6
<b>Mounting Hole Centers (Imperial)</b>	0.8
<b>Material</b>	Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Flammability**

UL 94 V2

**Operating Temperature (Metric)**

-40°F to +185°F (-40°C to +85°C)

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

100

**Package Quantity (Metric)**

100

**Customs Number**

3926909988