

## Specification Sheet

Part Number: MMB10H4



Masonry Cable Tie Mount, 1.712"L, .312" Hole Dia, .18" Max Cable Tie Width, PA66STHS, Black, 500/pkg

<b>Article Number</b>	151-00327
<b>Type</b>	MMB1
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Masonry Mounts provide a permanent solution when fastening wire and cables to masonry surfaces.</li><li>•The mounts have easy installation into predrilled holes allowing for faster use.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	HellermannTyton Masonry Mounts provide a permanent method of attaching wire and cable to masonry surfaces. Masonry mounts simply tap into predrilled holes and can be used for indoor and outdoor applications.
<b>Short Description</b>	Masonry Cable Tie Mount, 1.712"L, .312" Hole Dia, .18" Max Cable Tie Width, PA66STHS, Black, 500/pkg

Global Part Name

MMB1-PA66STHS-BK

Length L (Imperial)

1.712

Length L (Metric)

43.5

Fixation Method

with Fir Tree (Mounts)

Width W (Imperial)

0.508

Width W (Metric)

12.9

Cable Ties

T18 - T50

Height H (Imperial)

.50

Height H (Metric)

12.70

Cable Tie Width Max (Imperial)

0.18

Cable Tie Width Max (Metric)

4.6

Mounting Hole Diameter D (Imperial)

0.312

Mounting Hole Diameter D (Metric)

8.0 mm

Mounting Hole Diameter D Max (Metric)

8.0

Material

Polyamide 6.6, Super Tough, Heat Stabilized (PA66STHS)

**Material Shortcut**

PA66STHS

**Flammability**

UL 94 HB

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988