

## Specification Sheet

Part Number: 151-00429



Connector Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg

<b>Article Number</b>	151-00429
<b>Type</b>	EC42
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Head design contains clamping rails to provide full circumferential compression around bundles.</li><li>•Bent tail allows for quick insertion into head.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
<b>Short Description</b>	Connector Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg

**Global Part Name**

EC42-PA66HIRHS-BK

**Length L (Imperial)**

0.94

**Length L (Metric)**

24.0

**Fixation Method**

Edge Clips

**Width W (Imperial)**

0.53

**Width W (Metric)**

13.4

**Panel Thickness Min(Imperial)**

0.06

**Panel Thickness Max(Imperial)**

0.16

**Panel Thickness Min (Metric)**

1.5

**Panel Thickness Max (Metric)**

4.0

**Material**

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

**Material Shortcut**

PA66HIRHS

**Flammability**

UL 94 HB

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

1.377