

## Specification Sheet

Part Number: HDM190HIRH4



Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.1875", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg

Article Number	151-00436
Type	HDM19
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Mount and tie combination makes it easy to service bundles in the field.</li><li>• Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.</li><li>• Eliminates the needs for multiple sized fix diameter clamps.</li></ul>
Quantity Per	bag
Product Description	These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

<b>Short Description</b>	Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.1875", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg
<b>Global Part Name</b>	HDM19-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.43
<b>Length L (Metric)</b>	36.3
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.76
<b>Width W (Metric)</b>	19.3
<b>Height H (Imperial)</b>	0.66
<b>Height H (Metric)</b>	16.7
<b>Cable Tie Width Max (Imperial)</b>	0.50
<b>Cable Tie Width Max (Metric)</b>	12.7
<b>Mounting Hole Diameter D (Imperial)</b>	0.1875
<b>Mounting Hole Diameter D (Metric)</b>	4.7 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.1875
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.1875
<b>Mounting Hole Diameter D Max (Metric)</b>	4.76

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>Maximum Torque (kgf-cm)</b>	132.5
<b>Maximum Torque (lbf-ft)</b>	9.583
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Weight (Imperial)</b>	0.00964