

## Specification Sheet

Part Number: HDM250HIRH4



Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg

<b>Article Number</b>	151-00438
<b>Type</b>	HDM25
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Mount and tie combination makes it easy to service bundles in the field.</li><li>• Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.</li><li>• Eliminates the needs for multiple sized fix diameter clamps.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

**Short Description**

Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg

**Global Part Name**

HDM25-PA66HIRHSUV-BK

**Length L (Imperial)**

1.41

**Length L (Metric)**

36.3

**Fixation Method**

Screw Mounting and Rivet

**Width W (Imperial)**

0.75

**Width W (Metric)**

19.3

**Height H (Imperial)**

0.66

**Height H (Metric)**

16.7

**Cable Tie Width Max (Imperial)**

0.50

**Cable Tie Width Max (Metric)**

12.7

**Mounting Hole Diameter D (Imperial)**

0.25

**Mounting Hole Diameter D (Metric)**

6.2 mm

**Mounting Hole Diameter D Min (Imperial)**

0.25

**Mounting Hole Diameter D Max (Imperial)**

0.25

**Mounting Hole Diameter D Max (Metric)**

6.2

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>Maximum Torque (kgf-cm)</b>	132.5
<b>Maximum Torque (lbf-ft)</b>	9.583
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Weight (Imperial)</b>	0.00912