

Specification Sheet

Part Number: HDM3120HIRC2



Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.3125", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

Article Number	151-00439
Type	HDM312
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Mount and tie combination makes it easy to service bundles in the field.• Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.• Eliminates the needs for multiple sized fix diameter clamps.
Quantity Per	bag
Product Description	These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Short Description

Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.3125", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

Global Part Name

HDM312-PA66HIRHSUV-BK

Length L (Imperial)

1.43

Length L (Metric)

36.3

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

0.76

Width W (Metric)

19.3

Height H (Imperial)

0.66

Height H (Metric)

16.7

Cable Tie Width Max (Imperial)

0.50

Cable Tie Width Max (Metric)

12.7

Mounting Hole Diameter D (Imperial)

0.3125

Mounting Hole Diameter D (Metric)

7.8 mm

Mounting Hole Diameter D Min (Imperial)

0.3125

Mounting Hole Diameter D Max (Imperial)

0.3125

Mounting Hole Diameter D Max (Metric)

7.9

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Maximum Torque (kgf-cm)	132.5
Maximum Torque (lbf-ft)	9.583
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Imperial)	0.00914

