

Specification Sheet

Part Number: ISO4X250H1



Isolator Mount for separating 0.25" Tubing, 0.25" Max Bundle Diameter, TPV, Black, 500/pkg

Article Number	151-00455
Type	ISO4X250
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Design provides quick and easy assembly.• Isolator mount dampens harmful vibrations on bundles• Material is durable, chemical and abrasion resistant, and remains flexible in low temperatures.
Quantity Per	carton

Product Description

HellermannTyton's isolator mount is used to align and separate 1/4" tubing or brake lines. Easy to assemble, the isolator dampens vibrations and can be used with up to four brake lines. Mounting the isolator can be accomplished with HellermannTyton's standard cable ties, button head ties, and any of HellermannTyton's heavy equipment mounts. Mounting is optional, but recommended for long runs. The isolator is durable, chemical and abrasion resistant, and remains flexible in low temperatures.

Short Description

Isolator Mount for separating 0.25" Tubing, 0.25" Max Bundle Diameter, TPV, Black, 500/pkg

Global Part Name

ISO4X250-TPV-BK

Width W (Imperial)

0.92

Width W (Metric)

23.4

Height H (Imperial)

1.36

Height H (Metric)

34.5

Material

Thermoplastic vulcanized (TPV) rubber

Material Shortcut

TPV

Flammability

UL 94 HB

Operating Temperature (Metric)

-110°F to +347°F (-79°C to +175°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.