

Specification Sheet

Part Number: 151-00629



Standoff Bundling Clip, 2.2" Long, Panel Thickness 0.03"–0.22", PA66HIRHS, Black, 3000/box

Article Number	151-00629
Type	SOC7FT6
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Clip can be installed by hand – no need for hardware or tools.•Design provides low insertion and high extraction force, for simple, secure performance.•Clip keeps bundle away from areas that could cause damage due to rubbing.
Quantity Per	box

Product Description

Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Short Description	Standoff Bundling Clip, 2.2" Long, Panel Thickness 0.03"–0.22", PA66HIRHS, Black, 3000/box
Global Part Name	SOC7FT6-PA66HIRHSUV-BK
Length L (Imperial)	2.2
Length L (Metric)	56.0
Offset Length(Imperial)	1.22
Offset Length(Metric)	31.0
Fixation Method	Fir Tree
Height H (Imperial)	0.9
Height H (Metric)	22.5
Panel Thickness Min(Imperial)	0.03
Panel Thickness Max(Imperial)	0.22
Panel Thickness Min (Metric)	0.70
Panel Thickness Max (Metric)	5.75
Mounting Hole Diameter D (Imperial)	0.25 - 0.27
Mounting Hole Diameter D (Metric)	6.4 - 7.1 mm
Mounting Hole Diameter D Min (Imperial)	0.25

Mounting Hole Diameter D Max (Imperial)

0.27

Mounting Hole Diameter D Max (Metric)

7.1

Material

Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

3000

Package Quantity (Metric)

3000

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.00154

Weight (Imperial)

0.00340

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)